























Strain Gauge - Linear Diaphragm

GAGE PATTERN <small>Actual size shown. Enlarged when necessary for definition.</small>				GAGE DESIGNATION Insert desired S-T-C number in spaces marked XX. (0, 5, 9, 11, 17, 23) ppm	RES.IN OHMS	ENCAPSULATION and LEAD WIRES OPTIONS AVAILABLE
Unit: millimeter						
LD7-350 <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  1.5X </div> </div>				Matrix Length: 12.25 Matrix Width: 5.75		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD7-350-PC-XX	350	E,L,LE,PXX
0.50	2.50	11.50	4.75			
LD7A-350 <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  1.5X </div> </div>				Matrix Length: 12.25 Matrix Width: 5.75		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD7A-350-PC-XX	350	E,L,LE,PXX
2.10	0.75	11.50	4.75			
LD7B-350 <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  1.5X </div> </div>				Matrix Length: 12.25 Matrix Width: 5.75		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD7B-350-PC-XX	350	E,L,LE,PXX
2.31	0.83	11.50	4.75			
LD7C-350 <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  1.5X </div> </div>				Matrix Length: 12.25 Matrix Width: 5.75		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD7C-350-PC-XX	350	E,L,LE,PXX
2.52	0.90	11.50	4.75			


Strain Gauge - Linear Diaphragm

GAGE PATTERN <small>Actual size shown. Enlarged when necessary for definition.</small>				GAGE DESIGNATION <small>Insert desired S-T-C number in spaces marked XX. (9, 11, 16, 23, 27) ppm</small>	RES.IN OHMS	LEAD WIRES OPTIONS AVAILABLE
<small>Unit: millimeter</small>						
LD8-3500 <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  2X </div> </div>				Matrix Length: 8.40 Matrix Width: 5.50		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD8-3500-PC-XX	350	E,L,LE,PXX
1.10	4.32	7.24	4.70			
LD8-2500S <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  2X </div> </div>				Matrix Length: 8.40 Matrix Width: 7.20		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD8-2500S-PC-XX	2500	E,L,LE,PXX
1.60	5.89	7.69	6.40			
LD8-500N <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  2X </div> </div>				Matrix Length: 8.40 Matrix Width: 5.50		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD8-500N-PC-XX	500	E,L,LE,PXX
1.20	4.12	7.24	4.70			
LD9-350M <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  1.5X </div> </div>				Matrix Length: 10.60 Matrix Width: 5.30		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD9-350M-PC-XX	350	E,L,LE,PXX
1.30	1.77	9.52	4.27			


Strain Gauge - Linear Diaphragm

GAGE PATTERN <small>Actual size shown. Enlarged when necessary for definition.</small>				GAGE DESIGNATION <small>Insert desired S-T-C number in spaces marked XX. (0, 5, 9, 11, 17, 23) ppm</small>	RES.IN OHMS	ENCAPSULATION and LEAD WIRES OPTIONS AVAILABLE
<small>Unit: millimeter</small>						
LD12-350 <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  1.5X </div> </div>				Matrix Length: 13.68 Matrix Width: 4.84		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD12-350-PC-XX	350	E,L,LE,PXX
1.00	2.65	12.00	4.01			
LD12B-350 <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  1.5X </div> </div>				Matrix Length: 13.00 Matrix Width: 5.50		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD12B-350-PC-XX	350	E,L,LE,PXX
1.00	3.23	12.00	3.93			
LD16-350 <div style="text-align: center;">  1X </div>				Matrix Length: 18.24 Matrix Width: 6.45		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD16-350-PC-XX	350	E,L,LE,PXX
1.27	3.53	16.00	5.35			
LD20-350 <div style="text-align: center;">  1X </div>				Matrix Length: 21.00 Matrix Width: 6.50		
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD20-350-PC-XX	350	E,L,LE,PXX
1.80	4.98	20.00	4.98			



Strain Gauge - Linear Diaphragm

GAGE PATTERN Actual size shown. Enlarged when necessary for definition.				GAGE DESIGNATION Insert desired S-T-C number in spaces marked XX. (9, 11, 16, 23, 27) ppm		RES.IN OHMS	LEAD WIRES OPTIONS AVAILABLE
Unit: millimeter							
LD20B-350N <div style="text-align: center;">  1X </div>				Matrix Length: 21.40 Matrix Width: 6.50			
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH			350	E,L,LE,PXX
0.90	4.81	19.80	5.20				
				LD20B-350N-PC-XX			

Strain Gauge Copper on Constantan



Strain Gauge - Linear Diaphragm

GAGE PATTERN Actual size shown. Enlarged when necessary for definition.				GAGE DESIGNATION Insert desired S-T-C number in spaces marked XX. (9, 11, 16, 23, 27) ppm		RES.IN OHMS	LEAD WIRES OPTIONS AVAILABLE
Unit: millimeter							
LD1B-K350Q <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  1X </div> <div style="text-align: center;">  1.5X </div> </div>				Matrix Length: 12.90 Matrix Width: 4.00			
GAGE LENGTH	GRID WIDTH	OVERALL LENGTH	OVERALL WIDTH	LD1B-K350Q-PC-XX		350	E,L,LE,PXX
1.00	2.50	11.90	2.50				