


Static Measurement Software TDS-7130v2

TDS-7130v2-A (Special version applicable to long-term measurement and alarm contact) TDS-7130v2-C (Special version applicable for taking pictures using a webcam)



The TDS-7130v2 runs on a MS Windows PC to perform static measurement using TML data loggers. In addition to visual representation with multiple graphs, this software is a powerful tool for creating a report with data and graphs because it is capable of pasting multiple graphs, value monitors, labels and images on one graph sheet. It can take the most advantage of the data logger function of automatic multi-channel measurement.

The TDS-7130v2-A, applicable to long-term measurement and alarm contact, is optionally available. It has additional functions including automatic start of measurement, alarm output using contact unit, and automatic scroll of progress monitor. The TDS-7130v2-C, applicable to use multiple webcams to view the status of the measurement target and to save webcam images as still images during measurementWith these functions, the software is suitable for observation during and after construction, and construction management.

- User interface design compatible with wide-screen display
- Number of measuring times is 20 million at the maximum; applicable to long-term continuous measurement.
- For interval timer and data comparator, 8 tables can be created and executed respectively.
- 9 data lists for optional data items can be created in addition to original data list for all data items; data output can be modified according to processing.
- Continuous measurement by every 0.1 seconds is possible corresponding to high speed mode of TS-960/-963 and TDS-630.
- Two or more graphs are indicated on one graph sheet.
- Vector monitor and arrow monitor are indicated on graph sheet.
- Storage and reproduction of screen layout



Tokyo Measuring Instruments Laboratory Co., Ltd.


Setting sheet

Setting sheet is a file for setting measurement conditions, and recording and listing data. It consists of nine items as instrument I/F, measurement conditions, coefficient setting supplement, TML-NET, interval measurement, data comparator measurement, check results, data table, and data list. Setting sheets can be switched by task or menu.

- The maximum number of measurement can be increased from 50 thousand times to 20 million times by changing the maximum number of data items from 4000 points to 10 points.
- Each 8 tables can be created and executed for both of interval timer and data comparator.
- One data list for all items and 9 data lists for optional items can be created for data output corresponding to data processing.

Setting sheet

Menu is always displayed by dragging the horizontal line part of the top of the menu. This is convenient for frequently used menu.



Function panel

unction panel		
No.2=		~
Adapt		-
Check Function is not set.		
Insert + • * / () Select data	
Function list	Туре	^
ABS(value or expression)	Math functions (absolute)	
ACOS (value or expression)	Trigonometric function	
ASIN (value or expression)	Trigonometric function	
ATAN (value or expression)	Trigonometric function	
CH(switching box ch.number)	Measurement information function	(measureme *
4 11		

Function panel makes it easy to input Ch. No./ Function equation.

Graph sheet, Free form

Various graphs, images, drawings and value monitor can be arranged freely.

- · Possible to display two or more free forms and/or graph sheets at the same time
- Two or more graphs can be arranged on one graph sheet.
- Monitor point can always be displayed in the graph.
- Graph can be updated according to data by specifying the number of measurements for graph drawing or by enabling automatic updating by measurement.
- Regression line can be drawn from the measurement result.
- Windows of setting sheets and graphs can be gathered in one window by using tab display.
- Display location of all displayed windows can be saved into and reproduced from layout file.


• Line graph Line/Scatter



Regression line is drawn from the measurement result


• Distribution chart X/Y bar graph

A/ T bar gra




distribution chart which are input into Op.Data.

Progress graph




Progress monitor (option)



Draws progress graph by optionally specified days or hours. This is available with TDS-7130v2-A.

X/Y graph distribution

Draws T-Y graph



Additional object

Value monitor

Stophinsge							
Value monitor							
ch-1		ch-2			ch-3		
38		81		171			
Name	ch-	4	ch-5	;	ch-6		
Current	12	4	221		263		
Maximum	14	9	254		302		
Minimum	-32	2	-64		-73		

Value monitor is added on the free sheet or graph sheet. Name, current value, maximum/ minimum value and unit can also be indicated. Items satisfying the alarm condition are indicated in a different color.

Characters	
Graph2.ts 🗖 🗉 🖾	
Character object	
Character object	
Font, Font size to change	
Color change	
Border, shadow	

Comment and title can be added optionally on free form and graph sheet.

Principal stress and strain are indicated by arrow. The line color changes when the alarm condition is satisfied.

26

15

47.9


Vector monitor

— 10 uStrain

Vector moniter(3 - axis)

Minimum principal strain

of maximum principal strair




Direction and magnitude are indicated by arrow. The line color changes when the alarm condition is satisfied.

Automatic measurement

Interval measurement, data comparator measurement, alarm measurement, and alarm interval measurement can be performed for automatic measurement under various conditions.

- The interval measurement can be performed simultaneously at a set time interval with up to 8 different settings.
- Data comparator measurement, which measures the amount of change in a set measurement item, can be performed simultaneously with up to 8 different settings.
- The alarm measurement can be performed when the alarm condition is met.
- Alarm interval measurement can be performed to start interval measurement when alarm conditions are met.

Free run measurement



Free run measurement eliminates standby time and provides the fastest continuous measurement in the operating environment.Compatible with TS-960/-963 and TDS-630's high-speed repeatability of 0.1 second for up to 1000 points, enabling measurement at 0.1-second intervals.

Measurement system

Example of basic system using TDS-7130v2



TDS-7130v2-A (applicable to long-term measurement and alarm contact)

For the TDS-7130v2-A, the following functions are added to those of the TDS-7130v2.

- Controls an external alarm device and transmits the alarm occurrence outside the PC.
- Automatically opens measurement panel and starts specified automatic measurement.
- Automatically saves the text file of data list which is optionally specified during measurement.
- When alarm occurs, creates text file of alarm occurrence conditions.
- Draws progress graph by optionally specified days or hours.

Additional functions



Draws an elapsed chart in days or hours from the most recent data.

Data for the most recent period can always be plotted.



Automatically enters the measurement state when the specified setup sheet is read. Can be used for automatic recovery from power failure.

Measurement system




Optional Products

H	
*	

Saves selected data lists and alarm occurrences to a text file as measurements are made. The measurement data can be used by other software.

Alarm output	
Revolving light	BOC-2Hd
Network Relay Contact Unit PHN	Relay Contact Unit -R PHC-D08
Relay contacts are cont status. Any device that can be contact can be used, ex	



TDS-7130v2-C (applicable for taking pictures using a webcam)

For the TDS-7130v2-C, the following functions are added to those of the TDS-7130v2.

- The software displays the status of the measurement target using multiple webcams.
- Webcam image at the time of measurement can be saved as a still image
- Webcam images can be inserted into graph sheets and blank forms

• Photos taken with a digital camera can be inserted into graph sheets or blank forms, synchronizing the date and time the photo was taken with the date and time of the measurement.

• Graphs and pictures on a graph sheet can be automatically played back within a specified step range.

Video panel




The video images of the webcams used are always displayed.

You can switch between displaying only one camera or all of them at the same time.


Save each still image to a file at the time of measurement.

Photo object



JPEG files taken with a digital camera or other device and saved on a computer are displayed on the graph sheet. Synchronizes with a file whose shooting date and time is close to the measurement date and time of the specified step.

Measurement system



Video monitor




Optional Products

Displays images from the selected webcam on a graph sheet.

While monitoring, the image of the video panel is always displayed, and while monitoring is stopped, the file synchronized to the specified step is displayed.

Continuous Replay



The display steps of various objects on the graph sheet are updated at regular intervals and the test progress is automatically replayed.

Specifications

Measurement condition

Maximum number of data items

To be set between 10 and 4000 (including calculation result)

- Maximum number of measurement 50,000 ~ 20,000,000 times (varies depending on the setting of
- number of data items) Depends on the capacity of installed memory and disk.

Setting item

Name, Ch.No./Function, Unit, Format, Measurement mode, Offset value, Sensor mode, Optional data, Alarm

Interval measurement

8 tables can be set and executed simultaneously.

Data comparator measurement 8 tables can be set and executed simultaneously.

Measurement mode

Monitor, Manual measurement, Interval measurement, Data comparator measurement, Free run measurement, Alarm measurement, Alarm interval measurement, Data input measurement, Stroke change, Initial measurement, Check

Alarm display

Displays alarm occurrence status on the alarm panel and monitor according to the alarm condition set by the measurement condition. Data list Following lists can be displayed.

1 data list to show all measured data for every measurement date 9 data lists to show measured data for optionally selected items

Maximum/Minimum value display

Maximum and minimum values for every data item are displayed in the data list

Data table

Optional measurement data can be displayed in a table by specifying the number of measurement

Check result

Displays direct value in initial measurement and result of checking Reading data recorded by data logger

Reads data stored in recording media by connecting the media to a PC

Reads data directly from recording media of the data logger

Graph

Free form, Graph sheet

Various graphs, images, drawings and value monitor are arranged freely.

Two or more free forms and/or graph sheets can be displayed simultaneously.

Two or more graphs can be arranged on one graph sheet.

Saving and reproduction of layout

Display location of all displayed setting sheets, free forms and graph sheets are saved into file, and the display is reproduced by reading the file.

Type of graphs

Line, Scatter, Progress, Vertical bar graph, Horizontal bar graph, X graph distribution, Y graph distribution, Value monitor, Vector monitor, Arrow monitor

Saving of measurement data

Measurement data are saved in the same setting sheet as the measurement condition.

Saved automatically at every measurement.

Text conversion: Measurement data are saved in text format file (separated by tab) or in CSV format file (separated by comma). Saving of free form and graph sheet

Conversion of free form and graph sheet

Since free form and graph sheet can be saved in BMP, EMF or PNG format, they can be read using commercially available software, and graphs can be modified.

Text conversion of graph: Saves all data displayed in the graph in text format file (separated by tab) or in CSV format file (separated by comma).

Operating environment					
OS	Microsoft Windows 7(SP1), 8.1, 10, 11				
Computer	Model which satisfies the specifications recommended by				
	the above OS and also has USB port (Dual core or more),				
	CD drive				
Interface					
GP-IB	Manufactured by National Instruments Corporation or				
	CONTEC Co., Ltd.				
RS-232C	COM 1 ~ 8				
USB	USB2.0				
LAN	10BASE-T/100BASE-TX				

Conditions for applicalbe data logger/instrument

Applicable	Applicable	Interface			Measuring	
instrument	version	LAN	USB	RS-232C	GP-IB	points
TS-960/-963		0	0	0		1000
TS-560		0	0	0		1000
TS-360		0	0	0		1000
TDS-540	1.0C or later	0	0	0		1000
TDS-630	1.1C or later	0	0	0		1000
TDS-530	1.0C or later	0	0	0		1000
TDS-150		0*	0	0		100
DRA-30A	1.0B or later		0		0	300
NIF-100	1.0D or later			0		100
TC-35N				0		100
THS-1100	1.1A or later			0	0	1000
THS-1000					0	500
TDS-602	1.0G	0 *		0	0	1000
TDS-601	1.4A or later			0	0	1000
TDS-601A	1.4A or later			0	0	1000
TDS-303	1.0Eor later	0		0	0	1000
TDS-302	1.2Aor later			0 *	0	1000
TDS-300				0		250
TDS-102	1.0F or later			0		100
	1.0F or later					

*: Option

Related products

USB - RS-232C serial conversion adaptor

This is an adaptor to convert RS-232C connection of instrument into USB connection.

USB-RSAQ6 manufactured by I-O Data Device, Inc.

GP-IB interface

This is an extended interface used for connecting an instrument having GP-IB interface to a personal computer. The TDS-7130v2 is applicable to GP-IB interface manufactured by National Instruments Corporation or by CONTEC Co., Ltd.

• PCI-GPIB, etc. manufactured by National Instruments Corporation

• GP-IB(PCI)F, etc. manufactured by CONTEC Co., Ltd.

Relay unit (when using TDS-7130v2-A)

- Personal computer output relay unit PHC-100A/PHC-100
 manufactured by PATLITE Corporation
- Network relay control unit PHN-R manufactured by PATLITE Corporation



Approval Certificate **ISO9001** Design and manufacture of strain gauges, strain measuring equipment and transducers Visual LOG is a registered trade mark of Tokyo Measuring Instruments Laboratory Co., Ltd.

The contents of this catalog are subject to change without prior notice. The contents of this catalog are as of December 2024. TML Pam E8002C.



8-2, Minami-ohi 6-chome, Shinagawa-ku, Tokyo 140-8560, JAPAN TEL: +81-3-3763-5614 FAX: +81-3-3763-6128

